

Thermoset ME-455-1 Board Level Encapsulant

Description

LORD Thermoset ME-455-1 encapsulant is a low viscosity, one-component, semiconductor grade epoxy designed for the encapsulation of wire-bonded or flip chip die in PPGA, BGA, MCM and other cavity packages. It is formulated with high purity resins, fillers and additives to provide the ionic purity levels required for use in high-end microelectronic applications and minimize the chances of ion-induced corrosion in these devices.

Thermoset ME-455-1 encapsulant offers good adhesion to silicon, laminate, ceramic, solder mask and

metal surfaces. It can be used in demanding high-end, consumer and automotive applications.

Features and Benefits

Low Stress – exhibits low shrinkage and stress on components as it cures.

Low Coefficient of Thermal Expansion – minimizes the possibility of cracking during temperature cycling; provides excellent temperature shock performance.

Fast Cure – quickly cures at 150°C, leaving no pits or voids for a smooth surface.

Self-Leveling – rapidly flows into hard-to-reach spaces.

Typical Properties*

Uncured

Appearance	Black Liquid
Viscosity, cps @ 25°C	
Spindle 14, 10 rpm	7520
Specific Gravity	1.69
Gel Time, min @ 150°C	4
Working Life, hr @ 25°C	36

Cured

Volume Resistivity, ohm-cm @ 25°C	1×10^{15}
Coefficient of Linear Thermal Expansion, ppm/°C	
alpha 1, by TMA	21
alpha 2, by TMA	69
Glass Transition Temperature (Tg), °C	123
by TMA	
Hardness	92-98
Shore D	
Modulus of Elasticity, GPa	4
by DMA	
Dielectric Constant	3.37
1 MHz	
Dissipation Factor	0.006
1 MHz	
Extractable Ionic Contaminants, ppm	
Chloride	5
Sodium	5
Potassium	1

*Data is typical and not to be used for specification purposes.

LORD TECHNICAL DATA

Application

Applying – Before use with dispensing equipment, allow encapsulant to be warmed to room temperature (ideally 20-25°C). Thaw encapsulant by placing the syringe in a vertical (upright) position with dispense tip facing downward in an ambient environment. Consult handling instructions** for specific guidelines.

Mount the syringe onto the dispensing equipment that has been thoroughly cleaned and purge encapsulant through the system until an unbroken flow of encapsulant is extruded. The system is now ready to begin dispensing.

Curing – Allow encapsulant to cure for 30 minutes at 150°C. This time-at-temperature profile refers to the time the material should be allowed to cure once it reaches the target temperature. Allowance should be made for oven ramp rates, parts with large thermal mass and other circumstances that may delay material actually reaching the target temperature.

Shelf Life/Storage

Shelf life is six months from date of manufacture when stored at -40°C in original, unopened container. Syringe must be maintained at -40°C in a vertical (upright) position with the dispense tip facing down. Do not store syringe on its side (horizontally).

This material is shipped and stored frozen. Consult handling instructions** for thawing.

Cautionary Information

Before using this or any LORD product, refer to the Material Safety Data Sheet (MSDS) and label for safe use and handling instructions.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

***Handling instructions are available on LORD.com*

Values stated in this technical data sheet represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as LORD Corporation has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, LORD Corporation does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

"Ask Us How" is a trademark of LORD Corporation or one of its subsidiaries.

LORD provides valuable expertise in adhesives and coatings, vibration and motion control, and magnetically responsive technologies. Our people work in collaboration with our customers to help them increase the value of their products. Innovative and responsive in an ever-changing marketplace, we are focused on providing solutions for our customers worldwide ... Ask Us How.

LORD Corporation World Headquarters

111 Lord Drive
Cary, NC 27511-7923
USA

Customer Support Center (in United States & Canada)

+1 877 ASK LORD (275 5673)

www.lord.com

For a listing of our worldwide locations, visit LORD.com.

©2013 LORD Corporation OD DS3735 (Rev.2 8/13)

LORD
AskUsHow™