





Electrically Conductive Specialty Materials Selector Guide

Coatings, Adhesives, Sealants, Gap Fillers, and Greases

CHO-SHIELD®

Electrically Conductive Paints and Coatings

Product	Filler	Resin Type (Parts) Mix Ratio by Weight	Specific Gravity ¹	Max. Surface Resistance ¹ @ (Rec. Thickness ²) ohm/sq. (mils)	Min/Max. Use Temp. °C (°F)	Elevated Cure Schedule Time @ °C (°F)	RT Cure Schedule Time	Working Life Hours	Shelf Life Months ³	Theoretical Coverage @ Rec. Thickness ² ft ² /gram (m ² /gram)	VOC ⁴ g/L	Typical Application	Comments
2044*	Ni	Acrylic (1)	1.2	1.000 (2)	-40/85 (-40/185)	0.25 hr. @ 21 (70) + 0.75 hr. @ 66 (150)	24 hr.	Unlimited	12	0.034 (0.0032)	755	EMI shielding of electronic enclosures and assemblies	Durable coating. Nickel filler provides some H-field shielding
2056*	Ag/Cu & Ag	Acrylic (1)	1.1	0.030 (1)	-40/85 (-40/185)	0.25 hr. @ 21 (70) + 0.5 hr. @ 66 (150)	24 hr.	Unlimited	12	0.062 (0.0058)	718	EMI shielding of electronic enclosures and assemblies	Most cost effective EMI shielding solution for electronic enclosures
2040*	Ag	Acrylic (1)	1.2	0.025 (1)	-40/85 (-40/185)	0.25 hr. @ 21 (70) + 0.5 hr. @ 66 (150)	24 hr.	Unlimited	12	0.065 (0.0060)	741	EMI shielding of electronic enclosures and assemblies	Silver filler provides antimicrobial resistance and excellent EMI shielding
610*	Ag/Cu	Epoxy (3) A:B:C 100:42.4: 50	1.2	0.150 (2)	-65/125 (-85/257)	2 hr. @ 21 (70) + 1 hr. @ 66 (150) + 1 hr. @ 121 (250)	1 week	8.0	9	0.051 (0.0047)	591	Man portable electronics, radar systems, missile cannisters	Maintains electrical and mechanical stability in harsh environments
576*	Ag	Epoxy (2) A:B 100:27.5	1.7	0.060 (1)	-40/150 (-40/302)	1 hr. @ 21 (70) + 1 hr. @ 121 (250)	1 week	8.0	9	0.092 (0.0085)	560	Electroplating over plastics and graphite composites	Provides a conductive seed layer for electro-plating
596*	Ag	Epoxy (2) A:B 100:37.2	1.8	0.060 (1)	-40/150 (-40/302)	1 hr. @ 21 (70) + 1 hr. @ 121 (250)	1 week	8.0	9	0.098 (0.009)	585	Man portable electronics, radar systems, missile cannisters	Meets military specification MIL-C-22750, CHO-SHIELD 579 is a low VOC version of CHO-SHIELD 596
608*	Ag	Polyester (1)	1.4	0.015 (0.5)	-40/125 (-40/257)	0.25 hr. @ 21 (70) + 0.5 hr. @ 121 (250)	None	Unlimited	9	0.099 (0.0092)	711	EMI shielding of electronic enclosures and assemblies	Flexible coating, great for covering parts with difficult geometries
604*	Ag	Polyurethane (1)	1.2	0.010 (1)	-40/125 (-40/257)	0.25 hr. @ 21 (70) + 0.25 hr. @ 150 (302)	None	Unlimited	9	0.034 (0.0032)	767	Component level EMI shielding of semicon- ductor devices	Advanced coating developed for high volume, precise spray application on semiconductor packages
4994*	Ag	Polyurethane (4) A:B:C:D 100:18.3: 1.4:20.9	2.3	0.075 (3)	-40/85 (-40/185)	2 hr. RT & 40-60% RH + 2 hr. @ 54 (130)	1 week	3.0	6	0.030 (0.0028)	615	Airframes	Very smooth and very conductive; long pot life, excellent sprayability
2001*	Cu	Polyurethane (3) A:B:C 100:10.1:42.0	1.6	0.100 (3)	-65/85 (-85/185)	2 hr. @ 21 (70) + 0.5 hr. @ 121 (250)	1 week	2.0	9	0.035 (0.0033)	543	Corrosion protection for airframes	Requires use of CHO-SHIELD 1091 primer
2002*	Cu	Polyurethane (3) A:B:C 100:10.3:42.2	1.6	0.100 (3)	-65/85 (-85/185)	2 hr. @ 21 (70) + 0.5 hr. @ 121 (250)	1 week	2.0	9	0.035 (0.0033)	540	Corrosion protection for airframes	Chromate free. Requires use of CHO-SHIELD 1091 primer
2003*	Cu	Polyurethane (3) A:B:C 100:10.1:42.0	1.6	0.100 (3)	-65/85 (-85/185)	2 hr. @ 21 (70) + 0.5 hr. @ 121 (250)	1 week	2.0	9	0.036 (0.0033)	541	Corrosion protection for airframes	Requires use of CHO-SHIELD 1091 primer

CHO-BOND® and TECKNIT™

Electrically Conductive Sealants/Gap Fillers

Product	Filler	Resin Type (Parts) Mix Ratio by Weight	Specific Gravity ¹	Max. Vol. Resistivity ¹ ohm-cm	Min/Max. Use Temp. °C (°F)	Min. Lap Shear ¹ psi (kPa)	Elevated Cure Schedule Time @ °C (°F)	RT Cure Schedule Time	Working Life Hours	Shelf Life Months ³	VOC ⁴ g/L	Typical Application	Comments
CHO-BOND 4660*	Ag/Cu	Polyisobutylene (1)	2.0**	0.080	-55/100 (-67/212)	n/a	None	1 week ⁵	0.5	6	305	Sealing enclosure seams	Superior performance in vibration or shear. For vertical seams or longer (120 minutes) working life, use CHO-BOND 4669 VOC = 340.
TECKNIT 0005*	Ag/glass	Polyolefin (1)	1.7	0.005	-54/94 (-65/200)	4 (28)	None	24 hr.	5 min	9	419	Bonding enclosures	Flexible thixotropic cream system
CHO-BOND 2165*	Cu	Polyurethane (2) A:B 100:7	2.9	0.010	-65/85 (-85/185)	120 (827)	2 hr @ 21 (70) + 0.25 hr. @ 113 (235)	1 week ⁵	1.0	9	207	Airframe form-in-place sealing	Corrosion resistant; paintable
TECKNIT 0002	Ag	Silicone (1)	3.1	0.010	-59/204 (-75/400)	150 (1034)	None	72 hr.	5 min	5.5	31	Bonding elastomer gaskets	Rec. bond line thickness: 0.005" - 0.25" (- 0.13 mm - 6.35 mm); flexible paste; Handling time 24 hours.
CHO-BOND 1016*	Ni/C	Silicone (1)	2.4	0.500	-55/125 (-67/257)	150 (1034)	None	1 week ⁵	0.5	6	0	Ideal in outdoor applications for EMI shielding and low corrosion	Rec. bond line thickness: > 0.007" (0.18 mm); Primer promotes adhesion. Recommended primer is 1086
CHO-BOND 1038*	Ag/Cu	Silicone (1)	3.6	0.010	-55/125 (-67/257)	150 (1034)	None	1 week ⁵	0.5	6	111	Sealing enclosure seams; airframe gap sealing; connector shielding	Rec. bond line thickness: > 0.007" (0.18 mm); Primer promotes adhesion. Recommended primer is 1086 CHO-BOND 1121 is a solvent free version with a 12 month shelf life
CHO-BOND 1075*	Ag/Al	Silicone (1)	2.0	0.010	-55/200 (-67/392)	100 (689)	None	1 week ⁵	0.25	6	0	Sealing enclosure seams	Rec. bond line thickness: > 0.010" (0.25 mm) Primer promotes adhesion Recommended primer is 1086
CHO-BOND 1035*	Ag/glass	Silicone (1)	1.9	0.050	-55/200 (-67/392)	100 (689)	None	1 week ⁵	0.5	6	160	Sealing enclosure seams	Rec. bond line thickness: > 0.007" (0.18 mm) Primer promotes adhesion Recommended primer is 1086
CHO-BOND 1018*	Ni/Al	Polythioether (2)	2.1	0.200	-62/160 (-80/320)	65 (448)	None	1 week ⁵	2	6 @ -40°C	124	Sealing enclosure seams	Packaged in a pre-measured kit. No weighing required, mix and dispense in same package, minimizes process scrap.
CHO-BOND 1019*	Ag/Al	Polythioether (2)	2.15	0.010	-62/160 (-80/320)	65 (448)	None	1 week ⁵	2	6 @ -40°C	124	Sealing enclosure seams	Packaged in a pre-measured kit. No weighing required, mix and dispense in same package, minimizes process scrap.

CHO-BOND® and TECKNIT™

Electrically Conductive Adhesives

Product	Filler	Resin Type (Parts) Mix Ratio by Weight	Specific Gravity ¹	Max. Vol. Resistivity ² ohm-cm	Min/Max. Use Temp. °C (°F)	Min. Lap Shear ¹ psi (kPa)	Elevated Cure Schedule Time @ °C (°F)**	RT Cure Schedule Time	Working Life Hours	Shelf Life Months ³	VOC ⁴ g/L	Typical Application	Comments
CHO-BOND 584-29	Ag	Epoxy (2) 584:29 100:6.3	2.5	0.002	-55/125 (-67/257)	1200 (8274)	0.25 hr. @ 113 (235)	24 hr.	0.5	12	0.5	Bonding enclosures; connector shielding	General purpose; light paste; fast heat or RT cure; available in easy mix CHO-PAKs & SYRINGE-PAKs May be sprayed by thinning with toluene. CHO-BOND 584-29/toluene weight mix ratio is 100:150
CHO-BOND 584-208	Ag	Epoxy (2) 584:208 1:1	2.6	0.002	-62/100 (-80/212)	1000 (6895)	0.75 hr. @ 100 (212)	24 hr.	1.0	9	0	Bonding enclosures	General purpose; medium paste; fast heat or RT cure; Easy 1:1 mix ratio (wt.)
CHO-BOND 580-208	Ag	Epoxy (2) 580:208 1:1	2.9	0.003	-62/100 (-80/212)	700 (4826)	0.75 hr. @ 100 (212)	24 hr.	1.0	9	0	Bus bar grounding for shielded windows	May be sprayed by thinning with solvent. Solvent weight mix ratio is 50:30:20, toluene:butanol:propanol, CHO-BOND 580-208/solvent weight mix ratio is 100:38
TECKNIT 8116*	Ag	Epoxy (2) A:B 1:1	2.5	0.002	-62/100 (-80/212)	1400 (9653)	0.50 hr. @ 100 (212)	24 hr.	0.75	15	81	Bonding enclosures	Epoxy solder
CHO-BOND 360-20	Ag/Cu	Epoxy (2) 360:20 1:1	5.0	0.005	-62/100 (-80/212)	1600 (11032)	0.25 hr. @ 115 (239)	24 hr.	1.0	9	0	EMI gasket attachment; bonding enclosures	General purpose; very thick paste; fast heat or RT cure; Minimum bond line is 0.010" (0.25 mm)
CHO-BOND 1030*	Ag/Cu	Silicone (1)	3.8	0.050	-55/200 (-67/392)	200 (1379)	None	1 week ⁵	0.5	6	0	EMI gasket attachment	Recommended bond line thickness: < 0.010" (0.25 mm); Primer promotes adhesion. Recommended primer is 1086
CHO-BOND 1029*	Ag/Cu	Silicone (2) A:B 1:2.5	3.1	0.060	-55/125 (-67/257)	450 (3103)	0.5 hr. @ 121 (250)	1 week ⁵	2.0	6	14	EMI gasket attachment	Recommended bond line thickness: < 0.008" (0.20 mm); Primer promotes adhesion. Recommended primer is 1085
CHO-BOND 1077*	Ni/Al	Silicone (1)	2.4	0.600	-55/200 (-67/392)	250 (1724)	None	1 week ⁵	0.5	6	0	EMI gasket attachment; bonding enclosures	Greater than 250psi lap shear strength without an additional primer

CHO-LUBE® Electrically Conductive Grease

Product	Filler	Resin Type (Parts)	Specific Gravity ¹	Max. Vol. Resistivity ¹ ohm-cm	Min/Max. Use Temp. °C(°F)	Shelf Life Months ³	VOC ⁴ g/L	Typical Application	Comments
CHO-LUBE® 4220	Ag	Silicone (1)	3.1**	0.100***	-40/204 (-40/400)	12	0	Surface-to-surface particularly metal-to-metal sliding contact areas requiring continuous electrically conductive paths, such as a switch.	Can also be used for grounding of enclosures, equipment or components which require lubrication to overcome friction as well as EMI control. It may be supplied by standard caulking or grease guns.
CHO-LUBE E117	Ag/Ni	Silicone (1)	3.0**	0.040***	-55/200 (-67/392)	12	0	Silver-nickel filled silicone polymer designed for effective anti-wear of flanges and airframes.	Ideal for use in harsh, critical environments such as those found in aviation or defense applications.

** Wet density
*** Per CHO-MAT 1002

Ordering Information

Electrically Conductive Paints and Coatings

Product	Weight (grams)	Packaging	Chomerics Part No.	Primer Included
CHO-SHIELD 2044	3920	1 gallon aluminum can	52-03-2044-0000	Not Required
CHO-SHIELD 2056	4050	1 gallon aluminum can	52-03-2056-0000	Not Required
CHO-SHIELD 2040	4238	1 gallon aluminum can	52-03-2040-0000	Not Required
CHO-SHIELD 4900	122	6 fluid ounce aluminum aerosol can	52-02-4900-0000	Not Required
CHO-SHIELD 576	454	2 component, 1 pint aluminum can kit	52-01-0576-0000	Not Required
CHO-SHIELD 596	85	2 component, 1/2 pint aluminum can kit	52-00-0596-0000	Not Required
	454	2 component, 1 pint aluminum can kit	52-01-0596-0000	Not Required
CHO-SHIELD 579	454	2 component, 1 pint aluminum can kit	52-01-0579-0000	Not Required
CHO-SHIELD 610	3769	3 component, 1 gallon aluminum can	52-03-0610-0000	Not Required
CHO-SHIELD 608	1200	1 quart aluminum can	52-04-0608-0000	Not Required
CHO-SHIELD 4994	1802	4 component, 1 quart aluminum can kit	52-04-4994-1000	Not Required
	7210	4 component, 1 gallon aluminum can kit	52-03-4994-1000	Not Required
CHO-SHIELD 604	290	10 fluid ounce aluminum bottle	52-01-0604-0000	Not Required
CHO-SHIELD 2001*	250	3 component, 1/2 pint aluminum can kit	52-00-2001-0000	No
	250	3 component, 1/2 pint aluminum can "touch-up" kit	52-00-2001-1000	No
	700	3 component, 1 pint aluminum can kit	52-01-2001-0000	No
	1378	3 component, 1 quart aluminum can kit	52-04-2001-0000	No
CHO-SHIELD 2002*	250	3 component, 1/2 pint aluminum can kit	52-00-2002-0000	No
	250	3 component, 1/2 pint aluminum can "touch-up" kit	52-00-2002-1000	No
	700	3 component, 1 pint aluminum can kit	52-01-2002-0000	No
	1378	3 component, 1 quart aluminum can kit	52-04-2002-0000	No
CHO-SHIELD 2003*	250	3 component, 1/2 pint aluminum can kit	52-00-2003-0000	CHO-BOND 1091
	250	3 component, 1/2 pint aluminum can "touch-up" kit	52-00-2003-1000	No
	524	3 component, 1 pint aluminum can kit	52-01-2003-0000	CHO-BOND 1091
	700	3 component, 1 quart aluminum can kit	52-04-2003-0000	CHO-BOND 1091

Note: See Technical Data Sheet for packaging details
*** Requires the use of CHO-BOND 1091 Primer.**

Ordering Information

Electrically Conductive Paints and Coatings

Product	Weight (grams)	Packaging	Chomerics Part No.	Primer Included
CHO-BOND 4660	113.4	2 fluid ounce aluminum foil tube	51-02-4660-0000	Not Required
	681	0.1 gallon fiber cartridge	51-05-4660-0000	Not Required
CHO-BOND 4669	113.4	2 fluid ounce aluminum foil tube	51-02-4669-0000	Not Required
	681	0.1 gallon fiber cartridge	51-05-4669-0000	Not Required
TECKNIT 0002	56	0.75 fluid ounce aluminum foil tube	72-00002	Not Required
TECKNIT 0005	227	1 pint aluminum can	72-00005	Not Required
CHO-BOND 2165*	454	2 component, .5 pint aluminum can kit	50-01-2165-0000	No
	1135	2 component, 1 pint aluminum can kit	50-02-2165-0000	No
	2268	2 component, 1 quart aluminum can kit	50-04-2165-0000	No
CHO-BOND 1016	71	1.5 fluid ounce aluminum foil tube	50-02-1016-0000	CHO-BOND 1086
	300	6 fluid ounce SEMCO cartridge	50-01-1016-0000	CHO-BOND 1086
CHO-BOND 1038	113.4	1.5 fluid ounce aluminum foil tube	50-02-1038-0000	CHO-BOND 1086
	113.4	1.5 fluid ounce aluminum foil tube	50-02-1038-1000	No
	227	2.5 fluid ounce SEMCO cartridge	50-33-1038-0000	No
	454	6 fluid ounce SEMCO cartridge	50-01-1038-0000	CHO-BOND 1086
	454	6 fluid ounce SEMCO cartridge	50-31-1038-0000	No
CHO-BOND 1121	454	6 fluid ounce SEMCO cartridge	50-01-1121-0000	CHO-BOND 1086
CHO-BOND 1075	71	1.5 fluid ounce aluminum foil tube	50-02-1075-0000	CHO-BOND 1086
	71	1.5 fluid ounce aluminum foil tube	50-02-1075-1000	No
	284	6 fluid ounce SEMCO cartridge	50-01-1075-0000	CHO-BOND 1086
CHO-BOND 1035	71	1.5 fluid ounce aluminum foil tube	51-00-1035-0000	CHO-BOND 1086
	71	1.5 fluid ounce aluminum foil tube	51-00-1035-1000	No
	284	6 fluid ounce SEMCO cartridge	51-01-1035-000	CHO-BOND 1086
CHO-BOND 1018	280	6 fluid ounce SEMCO cartridge with dasher rod	50-01-1018-0000	Not Required
	120	2.5 fluid ounce SEMCO cartridge with dasher rod	50-02-1018-0000	Not Required
CHO-BOND 1019	280	6 fluid ounce SEMCO cartridge with dasher rod	50-01-1019-0000	Not Required

Note: See Technical Data Sheet for packaging details
*** Requires the use of CHO-BOND 1091 Primer.**

Ordering Information

Electrically Conductive Adhesives

Product	Weight (grams)	Packaging	Chomerics Part No.	Primer Included
CHO-BOND 584-29	1	2 component, premeasured CHO-PAK	50-10-0584-0029	Not Required
	2.5	2 component, premeasured CHO-PAK	50-02-0584-0029	Not Required
	10 x 3	2 component, premeasured, 10 x 3 gram syringe kits	50-30-0584-0029	Not Required
	10	2 component, premeasured CHO-PAK	50-03-0584-0029	Not Required
	85	2 component, 4 fluid ounce polypropylene kit	50-00-0584-0029	Not Required
	454	2 component, 8 fluid ounce polypropylene kit	50-01-0584-0029	Not Required
CHO-BOND 584-208	85	2 component, 4 fluid ounce polypropylene kit	50-00-0584-0208	Not Required
	454	2 component, 16 fluid ounce polypropylene kit	50-01-0584-0208	Not Required
CHO-BOND 580-208	227	2 component, 8 fluid ounce polypropylene kit	50-05-0580-0208	Not Required
	454	2 component, 16 fluid ounce polypropylene kit	50-01-0580-0208	Not Required
TECKNIT 8116	57	2 component, 2 fluid ounce polypropylene kit	72-08116	Not Required
CHO-BOND 360-20	85	2 component, 1/2 pint aluminum can kit	50-00-0360-0020	Not Required
	454	2 component, 1 pint aluminum can kit	50-01-0360-0020	Not Required
CHO-BOND 1030	113.4	1.5 fluid ounce aluminum foil tube	50-02-1030-0000	CHO-BOND 1086
	113.4	1.5 fluid ounce aluminum foil tube	50-02-1030-1000	No
	454	6 fluid ounce SEMCO cartridge	50-01-1030-0000	CHO-BOND 1086
CHO-BOND 1029	85	2 component, 4 ounce polypropylene kit	50-00-1029-0000	CHO-BOND 1085
	454	2 component, 8 ounce polypropylene kit	50-01-1029-0000	CHO-BOND 1085
CHO-BOND 1077	95	1.5 fluid ounce aluminum foil tube	50-02-1077-0000	Not Required
	325	6 fluid ounce SEMCO cartridge	50-01-1077-0000	Not Required

Note: See Technical Data Sheet for packaging details



Premeasured CHO-PAK



3 gram syringes



2-component kit with primer

Ordering Information

Primer

Product	Weight (grams)	Packaging	Chomerics Part No.
CHO-BOND 1085	400	1 pint can	50-01-1085-0000
CHO-BOND 1086	10	3 dram glass vial	50-10-1086-0000
	95	4 fluid ounce glass bottle	50-04-1086-0000
	375	1 pint can	50-01-1086-0000
CHO-SHIELD 1091	95	4 fluid ounce glass bottle	50-00-1091-0000
	375	8 fluid ounce plastic bottle	50-01-1091-0000

Note: Primers are applied to the substrate prior to application of the conductive material. In no instance is the primer to be mixed into the conductive material.



Ordering Information

Electrically Conductive Grease

Product	Weight (grams)	Packaging	Chomerics Part No.
CHO-LUBE 4220	113.4	1.5 fluid ounce foil tube	54-02-4220-0000
	283.5	6 fluid ounce SEMCO cartridge	54-01-4220-0000
CHO-LUBE E117	200	8 fluid ounce plastic container	54-01-E117-0200

Note: See Technical Data Sheet for packaging details

- * Hazardous shipping required. All compounds such as these should be packed and shipped by trained professionals. Regulations vary by material type and by quantity. The information provided here is to be used as a general guideline only.
- ** For alternate cure schedules csee Technical Bulletin.

1. Properties listed are for products prepared at the elevated cure schedule. Test Methods: Specific Gravity, 95-40-5504, 95-40-5502, QAP-1101F; Volume Resistivity, 95-40-5102, 95-40-5101, 95-40-6007, 95-40-6017; Surface Resistance, 95-40-5104; Lap Shear, 95-40-5300. These specifications are available from Parker Chomerics. Copies are available upon request.
2. The recommended thickness may vary from application to application. Please use the published data a preliminary guideline. Contact Parker Chomerics Application Engineering for assistance.
3. All Specialty Materials are shipped from Parker Chomerics with a minimum of 80% shelf life except for our polythioether materials (CHOBOND 1018 and CHOBOND 1019) which ship with a minimum of 60% shelf life remaining.
4. Volatile Organic Content (VOC) values are theoretical approximations calculated from the characteristics of the individual components of the product formulation.
5. Material is sufficiently cured after 24 hours for handling purposes. Full specification properties are developed after time given.

Parker Chomerics Contact Locations

To place an order please visit parker.com/chomerics or contact a Customer Service Representative at the following locations:

North America

Parker Chomerics Global Division Headquarters

77 Dragon Court
Woburn, MA
Phone +1 781-935-4850
Fax +781-933-4318
chomailbox@parker.com

Product Disclosure
(ROHS/REACH, Material Declarations, SDS)
choproductdisclosure@parker.com

Europe

Parker Hannifin Ltd
Chomerics Division Europe
Unit 6, Century Point
Halifax Road
High Wycombe
Bucks HP12 3SL
UK
Phone +44 1494 455400
Fax +44 14944 55466
chomerics_europe@parker.com

Asia Pacific

Parker Hannifin
Chomerics Shanghai
280 Yunqiao Road, Jin Qiao Export
Processing Zone, Shanghai 201206,
China
Phone +86 21 2899 5000
Fax +86 21 2899 5146
chomerics_ap@parker.com

Asia Pacific

Parker Hannifin
Chomerics Shenzhen
No.5 Bldg Jinrongda Technological Park
Gangtuo Village, Bantian Longgang District
Shenzhen, 518122, China
Phone +86 755 8974 8558
Fax +86 755 8974 8560
chomerics_ap@parker.com

Parker Hannifin
Chomerics Kula Lumpur
Lot 15, Jalan Gudang 16/9
Section 16, Shah Alam
Industrial Estate, 40200 Shah Alam
Selangor, Malaysia
Phone +603 5510 9188
Fax +603 5512 6988
chomerics_ap@parker.com

Penang, Malaysia
No.3, Puncak Perusahaan 1, 13600 Prai,
Penang, Malaysia
Phone +604 398329
Fax +604 3983299
chomerics_ap@parker.com

Parker Hannifin India Private Limited
Chomerics Division
Plot No. 41/2, 8th AvenueDTA, Anjur Village,
Mahindra World City, Chengalpattu, Tamilna-
du - 603 004, India
Phone +91 44 67132333
Phone +91 44 67132045
chomerics_ap@parker.com

Manufacturing Facilities

- Woburn, MA, USA
- Hudson, NH, USA
- Fairport, NY, USA
- Monterrey, Mexico
- High Wycombe, UK
- Frépillon, France
- Sadska, Czech Republic
- Kuala Lumpur, Malaysia
- Chennai, India
- Shanghai, China
- Shenzhen, China