

Chemlok® 7701 Surface Treatment

Technical Data Sheet

Chemlok® 7701 surface treatment is a solvent-based surface treatment for use on various vulcanized and thermoplastic polymeric materials. Chemlok 7701 surface treatment chemically alters the surface of the rubber, making it more receptive to bonding. Do not apply to metal surfaces.

Chemlok 7701 surface treatment is used in conjunction with a broad range of LORD adhesives, including epoxy and urethane adhesives, for bonding cured rubber. It improves adhesion to a variety of cured and thermoplastic polymeric materials, including natural rubber, synthetic polyisoprene, SBR, butyl, polybutadiene, neoprene, EPDM, nitrile, polyurethane, styrene-butadiene block copolymers, styrene isoprene rubbers and polyvinyl chloride.

Features and Benefits:

Versatile – functions as a cleaner and surface conditioner; treats a wide variety of elastomer functional materials.

Easy to Apply – applies easily by wipe, brush, dip or flood methods.

Convenient – requires no mixing.

Improved Adhesion – improves adhesion to cast urethanes and cured rubber.

Fast Drying – surface treatment flashes off within five minutes or less.

Environmentally Resistant – promotes increased environmental resistance by allowing the treated surface to be more easily wet.

Application:

Surface Preparation – Remove contaminants from rubber surface using a solvent wipe.

Applying – Apply surface treatment by wipe, brush, dip or flood methods. Spray application is not recommended due to the reactivity of the material.

Transfer the minimum amount of material necessary for the application into a new, clean container.

- **Wiping (preferred method)**
Apply surface treatment using a clean cotton rag. Change the rag frequently as it becomes contaminated with materials picked up from the surface being treated.
- **Brushing**
Apply surface treatment using a bristle or foam brush. Check foam-type brushes for compatibility before use. Use bristle brushes from man-made materials. Do not allow brushes with metal handles or metal collars to come in contact with the surface treatment.
- **Dipping**
Immerse parts in surface treatment. Place treated parts on a rack to allow excess material to drip off and the solvent to flash off.

To prevent contamination, discard excess material; do not return excess material to original container.

The treatment is complete after the solvent flashes off (<5 minutes). Rinsing is not necessary. The best bonds are achieved by assembling parts shortly after the solvent has flashed off. However, effective bonds have been obtained on parts stored under controlled conditions. Parts can be retreated, as necessary.

Cleanup – Use ethyl acetate for clean up. In the event of a spill, use large quantities of water to flush the area.

Typical Properties*

Appearance	Clear to Cloudy Liquid
Density kg/m ³ (lb/gal)	870 - 930 (7.3 - 7.8)
Solids Content by Weight, %	2.3 - 3.5
Flash Point (Seta), °C (°F)	-4 (25)
Solvents	Ethyl Acetate

*Data is typical and not to be used for specification purposes.

Shelf Life/Storage:

Shelf life is six months from date of shipment when stored by the recipient at 21-27°C (70-80°F) in original, unopened container.

Avoid storage in lighted areas. Store material in original container or UV-filtering plastic or glass container. Do not store in metal containers. Store Chemlok 7701 surface treatment in a cool, dark area away from oil, grease, sawdust, floor sweepings, easily oxidized organic compounds, ammonia, amines, ammonia salts, and metallic materials. Do not contaminate with water or alcohol.

Cautionary Information:

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Bond Performance of Epoxy Adhesive**

	Epoxy Adhesive to Natural	Epoxy Adhesive to SBR	Epoxy Adhesive to Nitrile
Chemlok 7701 Surface Treatment	40 - 50 pli 100% R	105 - 120 pli 100% R	75 - 85 pli 100% R

** Typical ranges reflect results of lab testing using LORD 305-1/305-2 adhesive (1:1 by weight) or LORD 320/310B adhesive (1:1 by weight).

R = Rubber Failure

0.3 cm x 15 cm x 2 cm (1/10" x 6" x 1") rubber part bonded to grit-blasted steel; cure 48 hours @ room temperature

ASTM D429-B 45° angle

Bond Performance of Castable Polyurethane

	Cast Urethane to Natural	Cast Urethane to SBR	Cast Urethane to Nitrile	Cast Urethane to Polychloroprene
Chemlok 7701 Surface Treatment	150 - 120 pli 100% R	75 - 85 pli 100% R, SB	70 - 80 pli 100% R	40 - 50 pli 100% R
No Treatment	10 - 15 pli 0% R	0 pli 0% R	40 - 45 pli 0% R	30 - 40 pli 0% R

R = Rubber Failure; SB = Stock Break

0.3 cm x 15 cm x 2 cm (1/10" x 6" x 1") rubber part bonded to grit-blasted steel; cure 48 hours @ room temperature

ASTM D429-B 45° angle

Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY: FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

©2023 Parker Hannifin - All Rights Reserved

Information and specifications subject to change without notice and without liability therefor. Trademarks used herein are the property of their respective owners.

OD DS3223E 12/23 Rev.5



Parker Lord
Engineered Materials Group

111 LORD Drive
Cary, NC 27511-7923
USA

www.Parker.com/EPM