

CHEMLOK® 8600 ADHESIVE

Technical Data Sheet

OBSOLETE

Chemlok® 8600 adhesive is a one-coat, water-based adhesive used to bond castable urethane elastomers to metal. Chemlok 8600 adhesive will also bond a wide variety of both polyether- and polyester-based urethanes of varying hardness to all types of metals.

Features and Benefits

Durable: provides a strong, durable bond that, in many instances, has strength equal to or greater than the tear strength of the urethane elastomer being molded.

Environmentally Preferred: has low VOC emissions.

Versatile: bonds a wide variety of both polyether- and polyester-based urethanes.

Process Compatible: accommodates a wide range of processing conditions, including extended prebake.

Convenient: requires only a single coat for most applications, reducing labor, inventory and shipping costs.

Elastomers

- Millable Urethane
- Castable Urethane
- Thermoplastic Urethane (TPU)

Application

Surface Preparation: Thoroughly clean metal surfaces prior to application. Remove protective oils, cutting oils and greases by solvent degreasing or alkaline cleaning. Remove rust, scale or oxide coatings by suitable chemical or mechanical cleaning methods.

For further detailed information on surface preparation of specific substrates, refer to Chemlok Adhesives application guide.

Mixing: Thoroughly mix adhesive before use. Do not shake. To prevent foaming, mechanical mixing should not exceed 60 rpm. The addition of anti-foaming agents is not recommended.

If dilution is needed, use deionized water. Slowly add water to the adhesive while mixing.

Applying: Apply adhesive by dip, spray or brush methods using stainless steel or plastic application equipment.

Regardless of application method, dry film thickness of Chemlok 8600 adhesive should be 30.5-40.6 micron (1.2-1.6 mil). If diluted, multiple coats may be required in order to attain the recommended film thickness.

Typical Properties*

Appearance	White Liquid
Viscosity, cps @ 25°C (77°F) Brookfield LVT Spindle 2, 30 rpm	200 - 600
Density kg/m ³ (lb/gal)	1018.5 - 1066.4 (8.5 - 8.9)
Solids Content by Weight, %	31 - 35
Flash Point (Seta), °C (°F)	≥93 (≥201)
Solvents	Deionized Water
pH	6.85

*Data is typical and not to be used for specification purposes.

Drying/Curing: Allow applied adhesive to air-dry for 30-60 minutes at room temperature. Drying time can be shortened by either preheating the metal parts or oven drying after application. Metal parts may be preheated to 49-60°C (120-140°F) prior to adhesive application. For coated parts, oven dry at 49-60°C (120-140°F) in a recirculating forced air oven.

To ensure optimum adhesion to the prepared metal surface, cure coated parts a minimum of 2 hours at 121°C (250°F). Large parts will require longer baking time at 121°C (250°F) to negate the heat sink effect.

Although optimum adhesion is achieved when molding is done shortly after adhesive has cured, coated parts may be stored up to one month before bonding if protected from contamination and excessive humidity. Large metal parts can be preheated up to 30 minutes at 148°C (300°F) or 16 hours at 100°C (212°F) without affecting adhesion when hot molding.

Molding procedures that are used with heat-vulcanizing urethane elastomers can be used with Chemlok 8600 adhesive. The cure time and temperature for bonding is the same as that required to vulcanize the urethane compound being molded. Best results are obtained with curing temperatures above 71°C (160°F).

Cleanup: Use soap and water to remove wet adhesive. Remove dried adhesive with alcohol or ketone-type solvents.

Shelf Life/Storage

Shelf life is six months from date of shipment when stored by the recipient in a well ventilated area at 21-27°C (70-80°F) in original, unopened container. Do not freeze product.

Parker Lord
Engineered Materials Group
111 LORD Drive
Cary, NC 27511-7923
USA
phone +1 877 275-5673
www.parker.com/EPM

DS3236 OD 10/24 Rev.7

Information and specifications subject to change without notice and without liability therefor.
Trademarks used herein are the property of their respective owners.

© 2024 Parker Hannifin Corporation



Cautionary Information

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.