


Wiring diagram

Installation ACC100


Revised: 7/2025

Connector DTM04-6P







- | | | |
|---|----------|--------|
| 1 | +5VDC | Red |
| 2 | Signal 1 | White |
| 3 | Ground | Black |
| 4 | +5VDC | Orange |
| 5 | Signal 2 | Yellow |
| 6 | Ground | Brown |

Mating connector: 01789ECD



Notes:

1. Recommended mounting screw diameter 1/4" or M6.
2. Do not exceed specified torque limit, 15 Nm.



For further information see:
Catalog HY33-2377/US

WARNING

FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS AND/OR SYSTEMS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker Hannifin Corporation, its subsidiaries and authorized distributors provide product and/or system options for further investigation by users having technical expertise. It is important that you analyze all aspects of your application, including consequences of any failure, and review the information concerning the product or system in the current product catalog. Due to the variety of operating conditions and applications for these products or systems, the user, through its own analysis and testing, is solely responsible for making the final selection of the products and systems and assuring that all performance, safety and warning requirements of the application are met.

The products described herein, including without limitation, product features, specifications, designs, availability and pricing, are subject to change by Parker Hannifin Corporation and its subsidiaries at any time without notice.

