


REV	ECR#	DESCRIPTION	DATE	BY	APP'D
A	E	DRAWN	03-14-2016	AH	—



CKT. #	PIN/TERM
SUPPLY	1
SIGNAL	3
Ground	2

NOTES:

1. PROGRAM SENSOR 0.5V @ -45°, 4.5V @ +45°
2. MECHANICAL:
ROTATIONAL ANGLE: APPROX. ±59° (118° TOTAL)
SPRING, CCW RETURN.
3. CTR - CTR OF MOUNTING HOLES = 1.5"
4. PRINTED ON LABEL: PARKER PART NUMBER, SERIAL NUMBER AND DATECODE (YWWXXXXXX)

TOLERANCES UNLESS OTHERWISE SPECIFIED

.00 ± .025"
 .00 ± .05"
 .00 ± .02"
 .000 ± .010"
 ANG ± 1°

- ⊗ - CRITICAL SYMBOL
- △ - LATEST REVISION SYMBOL
- ⊖ - INSPECTION SYMBOL



**Electronic Controls Division
Sensor Business Unit**

DATE: 03-14-2016	BY: AH	CH: —
TOOLING REV: N/A	MATERIAL: N/A	
TITLE: VA RS52 ROTARY SENSOR (01709)		
PROJ. NO: 1138	SIZE: A	DWG NO: 143557-CL
REV: A	SHEET: 1 OF 1	