



STARLETTE-PLUS-E (SPS) - R513A (sensor)

USER MANUAL REVISIONS	CLICK THE LINK TO ENTER YOUR REVISION OF USER MANUAL
SPS 004-100 small dryer (50Hz) 398H271660_Rev00	398H271660 Rev00 SPS-004-100 Multi-language
SPS 026-100 Energy saving small dryer (50Hz) 398H271661_Rev00	398H271661 Rev00 SPS-026-100-ES Multi-language
SPS 004-100 small dryer (50Hz) 398H271660_Rev01	398H271660 Rev01 SPS 004-100 Multi language
SPS 026-100 Energy saving small dryer (50Hz) 398H271661_Rev01	398H271661 Rev01 SPS 026-100 ES Multi language
SPS 004-100 small dryer (50Hz) 398H271660_Rev02	398H271660 Rev02 SPS004-100 Multi language
SPS 026-100 Energy saving small dryer (50Hz) 398H271661_Rev02	398H271661 Rev02 SPS026-100 ES Multi language
SPS 004-100 small dryer (50Hz) 398H271660_Rev03	398H271660 Rev03 SPS 004-100 Multi language
SPS 026-100 Energy saving small dryer (50Hz) 398H271661_Rev03	398H271661 Rev03 SPS 026-100 ES Multi language
SPS 004-100 small dryer (50Hz) 398H271660_Rev04	398H271660 Rev04 SPS 004-100 Multi language
SPS 026-100 Energy saving small dryer (50Hz) 398H271661_Rev04	398H271661 Rev04 SPS 026-100 ES Multi language
SPS 004-100 small dryer (50Hz) 398H271660_Rev05	398H271660 Rev05 SPS 004-100 Multi language
SPS 026-100 Energy saving small dryer (50Hz) 398H271661_Rev05	398H271661 Rev05 SPS 026-100 ES Multi language
SPS 004-100 small dryer (50Hz) 398H271660_Rev06	398H271660 Rev06 SPS 004-100 Multi language
SPS 026-100 Energy saving small dryer (50Hz) 398H271661_Rev06	398H271661 Rev06 SPS026-100ES Multi language
SPS 004-100 small dryer (50Hz) 398H271660_Rev07	398H271660 Rev07 SPS004-100 Multi language

STARLETTE-PLUS-E (SPS) - R513A (fan pressure switch)

SPS 004-100 small dryer (50Hz) 398H271742_Rev00	398H271742 Rev00 SPS-004-100-multi-language
SPS 026-100 Energy saving small dryer (50Hz) 398H271743_Rev00	398H271743 Rev00 SPS-026-100-ES-Multi-language
SPS 004-100 small dryer (50Hz) 398H271742_Rev01	398H271742 Rev01 SPS-004-100 multi-language
SPS 026-100 Energy saving small dryer (50Hz) 398H271743_Rev01	398H271743 Rev01 SPS-026-100-ES Multi-language
SPS 004-100 small dryer (50Hz) 398H271742_Rev02	398H271742 Rev02 SPS-004-100 multi-language
SPS 026-100 Energy saving small dryer (50Hz) 398H271743_Rev02	398H271743 Rev02 SPS-026-100-ES Multi-Language