



Plug-n-Play (PNP)


CARTRIDGE DUST COLLECTORS



ENGINEERING YOUR SUCCESS.




Protura® DH Nanofiber Technology



Protura DH nanofiber technology is a fine surface membrane applied to the filter substrate that prevents dust from penetrating into the filter pores and plugging the filters. Surface loading minimizes pressure loss and improves filter cleaning, extending filter life.

Protura DH Advantages

- Minimum Efficiency Reporting Value (MERV) 15 initial efficiency / 99.99% operational efficiency.
- Proprietary synthetic blend of fire retardant filter media conforming to UL 900 standards.
- Surface loading enhances dust release during filter cleaning which reduces emissions, noise pollution and compressed air consumption.



Machine Control Technology

- A bright, vivid interactive touchscreen controller makes our dust collectors easier than ever to operate and monitor, while reducing maintenance time.
- Monitors filter pressure drop for the primary and after-filters while alerting when filter change is required.
- Filter pulse cleaning settings including high/low set-points, continuous and downtime cycles.
- Provides external communication options for integration into remote alarms.
- NEMA 4X / IP65 rated providing the durability and reliability needed in harsh manufacturing environments.



Flow Control Technology

Easily adjust airflow to optimize system performance without use of mechanical dampers or complex and expensive variable frequency drives (VFD). It is critical to control air volume in dust collection applications because insufficient air volume leads to poor dust capture or insufficient transport velocity and pulling too much air shortens filter life and wastes energy.

- Rather than operating at full RPM at all times, you can adjust the fan to operate only when required, lower speed means **significant energy savings** over mechanical dampers, plus there will be less noise.

Optional Auto Flow

Air volume is measured and the fan automatically adjusts to maintain a specified target as process or filter pressure drop changes

Plug-n-Play (PNP)

The PNP offers best in class filter technology, easy to use and operate controls, energy efficiency with simplified maintenance and operation.

The DustHog® Plug-n-Play (PNP) cartridge dust collector provides a safe, effective and convenient solution to handle dust collection applications including thermally generated fumes from welding, laser / plasma cutting operations as well as other common nuisance dusts.

- **Filter Technology and Performance.**

Powered by Protura® DH nanofiber filter technology, the filters offer high operational efficiency, low operating pressure loss and reduced compressed air usage that can be relied upon to protect your workers and facility.

- **Easy to Operate.**

The PNP features an integrated touch screen controller that controls the fan and filter cleaning system. The interface alerts users when maintenance is required and allows users to manually or automatically adjust air volume as needed.

- **Energy Efficiency.**

An Electrically Commutated (EC) motorized impellor is featured on the PNP offering customers the latest in energy efficient technology.

- **Simplified Maintenance.**

Service convenience is built into the PNP offering single side access, tool-free filter removal and enhanced dust collection drawer.





Features & Benefits

Rear Compressed Air, Fire Suppression and Electrical Connection

Single point connections for supply voltage and compressed air.

Dirty Air Inlet

Rear inlet box with bolt pattern for a vertical duct connection.

Modern Look and Feel

Rounded corners and flush mount patches align product with target machine applications.

External Flange for Floor Mounting

Plate for anchoring unit to floor.

Dust Drawer

20 Gallon removable dust bin, with casters, pull handle, fork slots bottom emptying valve. Ramp included for easy and safe removal.



Safety After-Filter (Optional)

95% ASHRAE / HEPA After filter for toxic dust. Filter acts as unit silencer.



Integral Blower Module

Features motorized impellor with speed control for precise airflow control. Blower and controls are prewired with a single external termination.

Touchscreen Blower / Pulse Controls

Visual indication of system status and easy to understand operation. 24VDC wiring provides additional layer of product safety. Pulse cleaning options / adjustments.

Heavy Duty Construction

Heavy gauge steel construction with powder coated finish inside and out creating a durable and reliable product.

Simple Filter Maintenance

Cam-action mechanism and underside endcap handle facilitates fast, simple and tool-free filter removal and installation.



10 YEAR
WARRANTY



Technical Specifications & Filter Options

DustHog PNP Product Specifications


Model	Filter Media	Filter Configuration					Unit Dimensions					
		Width	Depth	Qty	Area		Width		Depth		Height*	
					(ft ²)	(m ²)	(in)	(mm)	(in)	(mm)	(in)	(mm)
PNP-12	ProTura DH	1	2	2	1,000	92.9	28.5	724	68.0	1,727	91.6	2,327
PNP-22	ProTura DH	2	2	4	2,000	185.8	57.0	1,448	68.0	1,727	91.6	2,327
PNP-32	ProTura DH	3	2	6	3,000	278.7	85.5	2,172	68.0	1,727	91.6	2,327

* Add additional 12.8" (325 mm) if after-filter option is included.

Sound level for products at nominal flow is approximately 78 dBA at 5 FT. With after-filter, sound level approximately 73 dBA at 5 FT.

Standard product voltage is 380-460 Volt / 3 Phase / 50-60 Hz.

Filter Options



Options and Accessories

- Safety after-filters
 - ASHRAE 95% / HEPA
- Slip, flanged and rolled flange inlet collars
- Remote control panel enclosure
- Auto flow air volume control
- Disconnect switch
- Additional integral blower options
- Additional filter media types and configuration options
- 575V Step down transformer
- Dust drawer liners
- Clean air discharge plenums
- Custom paint colors



Parker Hannifin is committed to providing clean air solutions that protect your employees, improve plant performance and enable you to realize your operating goals.

Our commitment is backed by continuous investment in research, leading-edge technology and product development, our people whom are the most knowledgeable in the industry, and a product portfolio that is proven to deliver results. We have been solving problems for you, our customers across the globe for over 50 years.

Industrial Applications

- Welding
- Plasma & Laser Cutting
- Bulk Powders
- Robotic Weld Cells
- Stone
- Fiberglass

Important – Understand and follow NFPA guidance in selecting equipment for your intended application, including required safety devices and testing your dust to determine combustion hazards. At your election, we can coordinate sample collection and testing.

Germany

Otto-Hahn-Strasse 6
D-65520 Bad Camberg
Germany
T: +49-6434-94220
Email: info@uas-inc.de
www.uas-inc.de

United Kingdom

Aston Lane North
Preston Brook
Runcorn, Cheshire
United Kingdom WA7 3GA
T: +44-1925-654321
Email: uas@clarcoruk.com
www.uasuk.com

China

1002 Unit 02-04, Floor 10
Tower I, Shanghai Arch
No.523 Loushanguan Rd, Shanghai
China
T: +86-21-52768288
Email: uasinfo@uasinc-cn.com
www.uasinc-cn.com

Industrial Gas Filtration and Generation Division

4087 Walden Avenue
Lancaster NY 14086 USA
Ph: 800-252-4647
Ph: 513-891-0400
dusthog@parker.com



ENGINEERING YOUR SUCCESS.