



1936



Bypass Lube Oil Sock Filter

1949



Dry Gas Filter

1953



Gas Filter-Separator

1955



Hook Vane

1965



Quick Opening Closure

1973



Cyclonic Cyclotube®

1981



Wave Plate Vane

1985



High Efficiency Vertical Gas Coalescer

1990



Cyclonic Mini-Cyclone

1995



PEACH® Cartridge Process

2004



Generation 2 performance level recipes for PEACH® Saturated Depth Coalescers

2003



PEACH® GOLD Cartridges

2002



ProComp VKO® Vertical Knock-Out Gas Coalescer

2001



PECO SafeLock Closure®

2000



Saturated Depth Coalescing™ with PEACH®

1999



Advanced Cyclotube® Blade Design

1998



PEACH Gemini PuraSep® Horizontal Gas Coalescer

2007



SafeLock 2 Closure



PEACH® Fusion

2008



PlantGard® On-Line Monitoring



XstreamPure® High Flow Liquid Filtration



Generation 3 performance level recipes for PEACH® Saturated Depth Coalescers



BlastPure® Auto-Clean Water Filtration System



TITAN PuraSep® Filter-Sep & Dry Gas Filters with EZ-Align®



Hot/Chem PEACH® Cartridges



BlastPure® Auto-Clean Water Filtration Modular System



PEACH Gemini PuraSep® 2 Horizontal Gas Coalescer



XstreamPhase® High Flow Liquid/Liquid Coalescer



Generation 2 XstreamSorb® Cartridges

2012

2013



VKC Cyclonic Technology

2014

2015



Chemelean® Economy Liquid Filtration

2016



XstreamSorb® Cartridges

2017

2019

2020