

Data sheet Quick connect coupling

Series 93

Coupling:			Plug: 93SF					DN: 8,1 = 52 mm ²	
Working pressure (static): 0 up to 15 bar									
Working temperature: -20°C up to +100°C (depending on the seal material and medium)									
Single shut of Double shut Straight throu Self venting Safety lock Dry Break	off		□ 1 ⊠ E □ F	Single hand wo hand op Ball locking s Pin locking s Coupling ant Plug anti-spl	peration system system ti-splash		Pipe-v U-Cup		
Materials:			S	tandard		Version			
Back body Valve body Valve Spring Seals Plug			teel, harde	ss, nickel plated rdened, DNC-PTFE- coated Brass AISI 301 Viton rdened, DNC-PTFE-					
Flug				coated					
Description: The 93KF series is a modular coupling and plug without an integrated locking system for installation in multi-coupling systems. The important sliding parts are coated with teflon to reduce frictional resistance as much as possible. The 93KF series are the parts of the multi-coupling 08 series. Interchangeability:									
Versions / special equipment (in part not for all versions, others upon request): seal material Buna N, Viton, Kalrez, Ethylen-Propylen; surface nickel plated, chrome plated, durnicoat; oil and grease free, silicon free;									
Test values at 20°C (depending on the version):									
Flow-rate air: 2600 l/min at 6 bar inlet pressure and 0,5 bar pressure drop Flow-rate water: 46 l/min at 0,5 bar pressure drop									
Vacuum coupling: Vacuum plug: Vacuum connected:		min %				ght coupling: app. 82 g ght plug: app. 85 g kage rate / dead volume: app ml			
Connecting force: Disconnecting force:		• • • • • • • • • • • • • • • • • • • •				bar inlet pressure app N bar inlet pressure app N			
Safety factor:		at least 4-times Burst-pressure:					at least	60 bar	
Fatigue: 5000 cycles connecting/disconnecting_tightness and function O.K.									
Revision	Date	Name		Date	Name	Document-no.:			
		1	Made.	22.07.04	schwab	1			
			Check	22.07.04	schwab	DB-93KF-SF-engl			