

## Data sheet Quick connect coupling

Series 96

Coupling: 96KS			Plug: 96SS						DN: 7,4 = 43 mm <sup>2</sup>	
Working pressure (static): 0 up to 35 bar										
Working temperature: -20°C up to +100°C (depending on the seal material and medium)										
Double shut	Safety lock		Single hand operati Two hand operati Ball locking syste Pin locking syster Coupling anti-splash			☐ Pipe- ⊠ U-Cu ☐ O-Riı		Pipe-\ U-Cup	RA-FLO-Valve	
Materials:				Standard		Version				
Back body Valve body Sleeve Valve Spring Locking Balls Seals Plug	Zalve body Eleeve Zalve Zing Spring ocking Balls / Pins Seals		Brass, nickel plated Brass, nickel plated Brass, nickel plated Zinc die-casting, nickel plated AISI 301 AISI 420 Buna N Brass, nickel plated							
Description: The series 96KS is a quick connect coupling with safety lock. To disconnect, the plug must first be pushed further into the coupling before it can be unlocked. This prevents unintentional disconnection. The series 96KS is a single hand operation coupling and has a high flow-rate due to the ULTRA-FLO-Valve. The series 96KS coupling ist not interchangeable with the series 95SS plug. The multitude of connecting options of the 96KS allows an universal use, for example breathing air, ring circuit system, lifting bas, weld and cut engineering, diving equipment.										
Interchangeability: CEJN 342										
Versions / special equipment (in part not for all versions, others upon request): seal material Buna N, Viton, Kalrez, Ethylen-Propylen; surface nickel plated, chrome plated, durnicoat; oil and grease free, silicon free;										
Test values	at 20°C (	depending	on the ver	sion):						
Flow-rate air: 1700 l/min at 6 bar inlet pressure and 0,5 bar pressure drop Flow-rate water: - l/min at 0,5 bar pressure drop										
Vacuum plug:		min. 87 % (rough vacuum) min % min %				Weight coupling: Weight plug: Leakage rate / dead volume:			app. 110 g app. 30 g app ml	
		w/o pressure app. 30 N w/o pressure app. 30 N				at 6 bar inlet pressure at 6 bar inlet pressure			app. 105 N app. 105 N	
Safety factor:		at least 4-times				Burst-pressure: at least 140 bar				
Fatigue: 5000 cycles connecting/disconnecting tightness and function O.K.										
Revision	Date	Name		Date	Name		Document-no.:			
I ICNISIOII	שמוט	ivallie	Made		Zahn		Document-110			
			Checl		Zahn			DB-9	96KS-SS-engl	

Stand.