



Parker Hannifin Corporation  
O-Ring & Engineered Seals Division  
2360 Palumbo Drive  
Lexington, KY 40509

February 1, 2023

Office 859 269 2351

Reference: V0894-90 End of Life

Dear Valued Customer,

We regret to share that the polymer used to make V0894-90 is being discontinued by our supplier. All current open orders will be fulfilled, but new orders will be required to move to a suitable alternative.

V0894 is a 90 durometer, brown fluorocarbon. V0894 is a general purpose fluorocarbon material with low compression set, and has a temperature range of -15 to 400°F. Replacement options are limited to black 90 durometer materials, including:

- VA090-90 for general purpose, black in color
- VA335-90 for PPAP O-rings, black in color

If you have any questions regarding the performance of V0894 compared to the other material options, please contact an Applications Engineer by calling 859-335-5101, or emailing [OESmailbox@parker.com](mailto:OESmailbox@parker.com).

Sincerely,

Dorothy Kern  
Applications Engineering Manager  
O-Ring & Engineered Seals Division  
[dkern@Parker.com](mailto:dkern@Parker.com)