



Parker Hannifin Corporation
O-Ring & Engineered Seals Division
2360 Palumbo Drive
Lexington, KY 40509

February 1, 2023

Office 859 269 2351

Reference: V1226-75 End of Life

Dear Valued Customer,

We regret to share that the polymer used to make V1226-75 is being discontinued by our supplier. All current open orders will be fulfilled, but new orders will be required to move to a suitable alternative.

V1226 is a 75 durometer, brown fluorocarbon. V1226 is an excellent, general purpose fluorocarbon material with low compression set, and has a temperature range of -15 to 400°F. V1226 is listed for UL service. V1226 has been certified to AMS7276. Replacement material options include

- VW076, brown in color, has the same UL service code listings
- VM330, black in color, is available with AMS7276 certification

If you have any questions regarding the performance of V1226 compared to the other material options, please contact an Applications Engineer by calling 859-335-5101, or emailing OESmailbox@parker.com.

Sincerely,

Dorothy Kern
Applications Engineering Manager
O-Ring & Engineered Seals Division
dkern@Parker.com