



Marine & Offshore

Certificate number: 74469/A0 BV

File number: .

Product code: 2104l

This certificate is not valid when presented without the full attached schedule composed of 7 sections

www.veristar.com

TYPE APPROVAL CERTIFICATE

This certificate is issued to

PARKER HANNIFIN MANUFACTURING S.r.I. Polymer Hose Division Europe

Veniano (CO) - ITALY

for the type of product

NON-METALLIC HOSES (FLEXIBLE PIPES) ASSEMBLIES

Non-metallic hose assemblies - Types 492-492ST-492TC

Requirements:

Bureau Veritas Rules for the Classification of Steel Ships Bureau Veritas Rules for the Classification of Offshore Units Bureau Veritas Rules for the Classification of Naval Ships

This certificate is issued to attest that Bureau Veritas Marine & Offshore did undertake the relevant approval procedures for the product identified above which was found to comply with the relevant requirements mentioned above.

This certificate will expire on: 13 Feb 2029

For Bureau Veritas Marine & Offshore, At BV NAPOLI, on 13 Feb 2024, Sandro BRUSEGAN

This certificate was created electronically and is valid without signature



This certificate remains valid until the date stated above, unless cancelled or revoked, provided the conditions indicated in the subsequent page(s) are complied with and the product remains satisfactory in service. This certificate will not be valid if the applicant makes any changes or modifications to the approved product, which have not been notified to, and agreed in writing with Bureau Veritas Marine & Offshore. Should the specified regulations or standards be amended during the validity of this certificate, the product(s) is/are to be re-approved prior to it/they being placed on board vessels to which the amended regulations or standards apply. This certificate is issued within the scope of the General Conditions of Bureau Veritas Marine & Offshore available on the internet site www.veristar.com. Any Person not a party to the contract pursuant to which this document is delivered may not assert a claim against Bureau Veritas Marine & Offshore for any liability arising out of errors or omissions which may be contained in said document, or for errors of judgement, fault or negligence committed by personnel of the Society or of its Agents in establishment or issuance of this document, and in connection with any activities for which it may provide.

Certificate number: 74469/A0 BV

THE SCHEDULE OF APPROVAL

1. PRODUCT DESCRIPTION

Type 492/492-ST/492-TC according to EN 857 1SC - ISO 11237 with 46 series

1.1 Ratings

Model	492	492-ST	492-TC
ND (mm)	6 to 31	6 to 31	6 to 25
Temperature range (°C)	-40 to 100	-40 to 100	-40 to 100
Max. Working Pressure (bar)	75 to 280	75 to 280	110 to 280

The Maximum Allowable Working Pressure in relation to temperature must be in conformity with manufacturer's specifications (depending on nominal diameter and temperature)

1.2 Materials

Part	Material	
Inner Tube	NBR	
Reinforcement	One high-tensile steel wire braid	
Cover	synthetic rubber	
	UHMWPE for "-ST"	

Fittings: 46 Series as per Catalogue in §2

When other choices of materials are used per manufacturer's recommendations, the BV agreement is to be obtained.

2. DOCUMENTS AND DRAWINGS

- Catalogue N° CAT/4400/UK dated 01/2021 (hoses and 46 series fittings)

No departure from the above documents shall be made without the prior consent of the Society. The manufacturer must inform the Society of any modification or changes to these documents and drawings.

3. TEST REPORTS

- 3.1 Type tests including burst test at 4 times the design pressure, visual inspection & dimensional check, change in length .
- Test report N° 3540, N° 3541 & N° 3555 dated 12/07/2022
- 3.2 Fire resistance test reports performed according to ISO 15540:1999:
- N° 737.0IS0110/04 dated 26/07/2004
- N° 738.0IS0110/04 dated 26/07/2004
- N° 739.0IS0110/04 dated 26/07/2004
- 3.3 Type tests reports (including burst test, ozone resistance test, cold flexibility test, impulse test, cover adhesion test):
- N° 047 to N° 053 dated 09/03/2023

4. APPLICATION / LIMITATION

- 4.1 May be used on the following services on board:
- Lubricating oil, hydraulic oil, thermal oil, fresh water, sea water, compressed air systems, bilge, ballast water, Class III steam systems
- 4.2 End fittings as per manufacturer's catalogue. The hoses are to be entirely assembled in the manufacturer's workshop.
- 4.3 The hoses are to be limited to a length necessary to provide for relative movement between fixed and flexibly mounted items of machine/equipment or systems. When the hoses are intended to be used for essential services or containing either flammable or toxic media, they are not to exceed 1.5 m in length. The hoses are to be installed in clearly visible and readily accessible locations at all times.
- 4.4 The hoses assemblies are to be installed according to manufacturer's instructions and Bureau Veritas Rules
- 4.5 The use of stainless steel is to be restricted as per the requirements of the Bureau Veritas Rules.
- 4.6 Tapered threaded end fittings are not to be used in engine rooms, nor in any place containing an ignition source unless otherwise suitably screened at the Society's Surveyor satisfaction.

Certificate number: 74469/A0 BV

4.7 - Not to be used in case of high level of vibrations where fitted to engines, pumps, compressors and other sources of high vibrations

5. PRODUCTION SURVEY REQUIREMENTS

- 5.1 The products are to be supplied by **PARKER HANNIFIN MANUFACTURING S.r.l. Polymer Hose Division Europe** in compliance with the type and the requirements described in this certificate.
- 5.2 This type of product certificate is within the category IBV of Bureau Veritas Rule Note NR320.
- 5.3 BV product certificate is required.
- 5.4 Each hose assembly is to be hydraulically pressure tested to 1.5 times the maximum working pressure and provided with the manufacturer's pressure test report and conformity of production.
- 5.5 For information, **PARKER HANNIFIN MANUFACTURING S.r.l. Polymer Hose Division Europe** has declared to Bureau Veritas the following production site:

PARKER HANNIFIN MANUFACTURING S.r.l. Polymer Hose Division Europe Via G.B. Pirelli,6 22070 Veniano (CO) ITALY

6. MARKING OF PRODUCT

Each flexible hose shall at least clearly and indelibly marked with:

- Manufacturer name or logo
- Date of manufacture (month/year)
- Type designation
- Nominal Diameter
- Pressure rating
- Temperature rating
- Society's brand as relevant

7. OTHERS

It is **PARKER HANNIFIN MANUFACTURING S.r.l. Polymer Hose Division Europe**'s responsibility to inform shipbuilders or their sub-contractors of the proper methods of fitting, use and general maintenance of the approved equipment and the conditions of this approval.

*** END OF CERTIFICATE ***