

Custom Products

For applications as unique as our customers.

aerospace
climate control
electromechanical
filtration
fluid & gas handling
hydraulics
pneumatics
process control
sealing & shielding



ENGINEERING YOUR SUCCESS.

You dream it. We machine it.


Customers' requirements are always different. So why work your designs around parts somebody else designed, just because that's what's readily available? Parker Tube Fittings Division can transform your unique concept into a finished part. That's right. We manufacture custom products to your specifications, drawings or world standards - whether you need thousands or just that one-of-a-kind.

Not just a capability, but an entire facility.

Parker custom products manufacturing facility was developed to do one thing: design and manufacture the custom fittings that were once considered out of reach for many projects. Available in almost any size and configuration, our custom tube fittings can be machined in steel, stainless steel, brass, and aluminum, as well as numerous other materials. As for quality standards, Parker's ISO 9001 facility produces fittings to comply with most of the various international standards, including, SAE, ISO, DIN, JIS, ASTM and MIL.

We're talking serious speed.

For us, prototype development, emergency repair and short runs are all in a typical day's work. With five shifts as well as computer numeric-controlled (CNC) lathes and machining centers working 24 hours a day, seven days a week, we can design and deliver products in the time it would take most manufacturers to simply devise a plan.





In fact, Parker has continued to invest in the latest CNC technology, adding several million dollars of new CNC equipment since 2009. We've also acquired an automated passivation system that allows same-day delivery on stainless-steel products; and have doubled the number of CNC operators from 2009 to 2012.

Many times, our **Rapid Service Unit (RSU)** can turn around requests for quotes on unusual configurations, jump sizes and prototypes the same day or inside 24, 48 or 72 hours depending on your requirement.

By focusing on making custom manufacturing customary, we can help reduce lead times, as well as the price of lower-volume parts.

So give us your ideas, even if they're sketchy.

Next time you've got a great idea, don't scrap it simply because you can't find the right part in a catalog. Call Parker toll free at **1-800-321-7732** and ask for custom fittings. Or e-mail inquiries regarding quotations to **customfittings@parker.com**. You just might be amazed at what we can draw up together.

Not only do we manufacture unique combinations of standard end types, Parker manufactures less conventional designs utilizing more of our machining expertise. We can use different materials, plating and seals as your application dictates.



Parker Fluid Connectors Group

North American Divisions & Distribution Service Centers

Your complete source for quality tube fittings, hose & hose fittings, brass & composite fittings, quick-disconnect couplings, valves and assembly tools, locally available from a worldwide network of authorized distributors.

Fittings:

Available in inch and metric sizes covering SAE, BSP, DIN, GAZ, JIS and ISO thread configurations, manufactured from steel, stainless steel, brass, aluminum, nylon and thermoplastic.

Hose, Tubing and Bundles:

Available in a wide variety of sizes and materials including rubber, wire-reinforced, thermoplastic, hybrid and custom compounds.

Worldwide Availability:

Parker operates Fluid Connectors manufacturing locations and sales offices throughout North America, South America, Europe and Asia-Pacific.

For information, call toll free...

1-800-C-PARKER
(1-800-272-7537)

North American Divisions

Energy Products Division

Stafford, TX
phone 281 566 4500
fax 281 530 5353

Fluid System Connectors Division

Otsego, MI
phone 269 694 9411
fax 269 694 4614

Hose Products Division

Wickliffe, OH
phone 440 943 5700
fax 440 943 3129

Industrial Hose Division

Strongsville, OH
phone 440 268 2120
fax 440 268 2230

Parflex Division

Ravenna, OH
phone 330 296 2871
fax 330 296 8433

Quick Coupling Division

Minneapolis, MN
phone 763 544 7781
fax 763 544 3418

Tube Fittings Division

Columbus, OH
phone 614 279 7070
fax 614 279 7685

Distribution Service Centers

Buena Park, CA

phone 714 522 8840
fax 714 994 1183

Conyers, GA

phone 770 929 0330
fax 770 929 0230

Lakeville, MN

phone 952 469 5000
fax 952 469 5729

Louisville, KY

phone 502 937 1322
fax 502 937 4180

Portland, OR

phone 503 283 1020
fax 503 283 2201

Toledo, OH

phone 419 878 7000
fax 419 878 7001
fax 419 878 7420
(FCG Kit Operations)

Canada

Grimsby, ONT

phone 905 945 2274
fax 905 945 3945
(Contact Grimsby for other Service Center locations.)

