

GLOBAL P3Y FRL'S

P3Y FRL system can be mounted as a separate threaded Filter, Regulator & Lubricator or easily combined into a modular FRL providing accurate pressure regulation, high moisture removal efficiency, and proportional oil delivery over a wide range of air flows.

- 3/4" and 1" (NPT & BSPP) port size
- 1-1/2" available with port block kits

Modular Accessory Modules

- Soft Start / Dump Valve
- Ball Valve
- Manifold

Advantages

- Quick delivery due to short lead times
- Body connectors do not add to the port to port dimension
- Polypropylene bowl has better chemical compatibility than polycarbonate

Value to Customer

- Complete range of modular accessories
- Increased production time due to clean dry air
- Decreased maintenance and downtime due to ease of assembly
- Space savings because of modular design

