

Together, we can
bring all of our
standard and custom
technologies under
one umbrella.



2-Way Solenoid Valves

Our history of designing and manufacturing 2-way valves allows us to offer a wide variety of standard products while providing easy modifications for custom solutions. Valve offerings range from general-purpose flow control to industry- and application-specific products.



INDUSTRIAL & COMMERCIAL EQUIPMENT • INSTRUMENTATION • LIFE SCIENCE • FOOD & BEVERAGE • COMPRESSORS •
TRANSPORTATION • ASSEMBLY CELLS • CONTROL PANELS • DIAGNOSTICS • FUEL DISPENSING



ENGINEERING YOUR SUCCESS.

2-Way Solenoid Valves

	Range	
Port Sizes (NPT)	1/8"	2.0"
Orifice Sizes	1/32"	1 1/2"
Pressure Rating	Vacuum	4,500 psi
Flow Factors (Cv)	0.02	38.6
Media Temperature	-40°F	353°F
Ambient Temperature	-40°F	150°F
Function	Normally Open, Normally Closed	
Body Material	Stainless Steel, Brass, Plastic	
Application Specific	High Pressure, Anti-Water Hammer, Manual Override, Dry Operator, Manifold Mount	



Parker Hannifin Corporation
Fluid Control Division
 1 800 825 8305
www.parker.com/fcd