



For Release: Immediately  
Contact: Lori Ragsdale  
Industrial Gas Filtration and Generation Division  
Phone 816 313 4496  
lori.ragsdale@parker.com

## **Parker Launches New SHM Machine Mount Mist Collector Making the SmogHog® Equipment Portfolio the Broadest in the Industry**

*Provides customers with mist collection technology options for their specific application, together with differentiated filter technology*

**Cincinnati, August 31, 2017** – The Industrial Gas Filtration and Generation Division of Parker Hannifin Corporation, the global leader in motion and control technologies, today announced the launch of the SmogHog SHM Machine Mount (MM) media mist collector. The SmogHog SHM MM is a media mist collector designed for direct mounted systems and collecting coolant mists from processes such as CNC machining, cold forming, sawing, lathes, stamping and more.

The SmogHog SHM MM unit is available in two base models rated at 500 CFM and 800 CFM to handle various machine sizes and applications. Both models feature PEACH® saturated depth coalescing media in a patent pending filter design. PEACH, a patented, proprietary Parker media technology uses a three-stage filtration process that progressively reduces the mist concentration resulting in greater than 99% particle removal efficiency. The 800 CFM unit is available in an advanced version that includes a remote touchscreen controller and EC blower, which simplifies product operation and maintenance while delivering energy savings.



“The introduction of the SmogHog SHM Machine Mount further expands our ability to solve our customer’s mist collection with a solution that best fits their needs,” said Travis

Haynam, product manager, Industrial Gas Filtration and Generation Division. “Having a comprehensive family of SmogHog mist collectors featuring best in class media and ESP technology allows us to provide appropriate solutions for a customer’s specific application that deliver value in meeting performance expectations and improved total cost of ownership.”

The industrial SmogHog SHM MM includes ASHRAE 95% oil mist or HEPA safety after-filter options, various wall mount alternatives, remote on/off disconnect switch, and many additional options and accessories including custom paint colors. Learn more about the SmogHog SHM MM at [www.uasinc.com](http://www.uasinc.com). To find a local SmogHog representative visit: <http://www.clarcorindustrialair.com/Rep> or call us +1-800-252-4647.

### **About Parker Hannifin**

Parker Hannifin is a Fortune 250 global leader in motion and control technologies. For 100 years the company has engineered the success of its customers in a wide range of diversified industrial and aerospace markets. Learn more at [www.parker.com](http://www.parker.com) or @parkerhannifin.

###