




SCS Series Installation Guide

SD-460 / 52020



1. COMPONENTS

Ensure all components are available:

A. SCS controller with attached:

- Coil out temperature sensor
- Pressure transducer cable
- Valve cable
- 120 VAC power cable

B. Pressure Transducer appropriate for the pressure range

C. Electric Expansion Valve (Stepper or Pulse) compatible with the SCS

D. DIN Solenoid Coil if Pulse Width Valve and Controller are used

- OR -

External stator with M12 connection if a Unipolar EEV is used.

2. INSTALLATION

Snap the QR code below to download [Bulletin 100-50-11.1, SCS Series Installation and Operation Instructions.](#)



[Bulletin 100-50-11.1](#)
[SCS Series Installation](#)
[and Operation Manual](#)

3. SETUP

Snap the QR code below to download the [Tech Check app](#) to your phone. This app will be used to configure the SCS controller.



⚠ WARNING – USER RESPONSIBILITY

Failure or improper selection or improper use of the products described herein or related items can cause death, personal injury and property damage.

This document and other information from Parker Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

